



EAGLE PROGRESSIVE

Recommended for: Everyone

PRIMARY PAIR

For a general purpose progressive lens that will fit the needs of most patients, we recommend the Eagle.

The Eagle is designed to meet the need of patients that want a progressive lens with a clear distance field of view. The distance is designed to be completely clear side-to-side, and still maintains a reasonable intermediate and near viewing zone. This is a feature that many patients look for in a progressive lens. A large, clear distance is especially important in activities such as outdoor recreation and driving.



AVAILABILITY

MATERIALS	POWER	ADD	FITTING HEIGHTS
<ul style="list-style-type: none"> Plastic Trivex Polycarbonate 	-20.00 to +12.00	+0.75 to +4.50	14mm
<ul style="list-style-type: none"> 1.56 1.60 1.67 1.74 	<u>CYLINDER</u>	<u>PRISM</u>	16mm
	0.00 to -12.00	0.00 to 7.00	18mm
	<small>Exact power range availability will vary depending on prescription, material, and frame measurements. Full power range not available in all materials</small>		
			20mm
			22mm

COLORS
<ul style="list-style-type: none"> Clear DayNite - Gray, Brown Polarized - Gray, Brown, G-15 LifeRx - Gray, Brown Transitions - Gray, Brown, XTRActive, Vantage Photofusion - Gray, Brown Drivewear
<small>Not all colors available in all materials.</small>

FEATURES

- Extra-Wide Distance Zone**
Perfect for driving or outdoor activities.
- Variable Decentration**
Accomodate large frames and PDs that most other progressives can't handle.
- Variable Inset**
Optimized near viewing area tailored to each patient.
- Minimized Oblique Astigmatism**
Clear vision across the entire surface of the lens.

- Lenticularization**
Minus lenses in wrap frames are no longer a problem.
- Advanced Frame Measurements**
 - Pantoscopic Tilt**
How vertically straight or tilted the frame is when worn.
 - Vertex Distance**
Distance between eye and lens.
 - Wrap Angle**
Degree to which the frame curves to fit the patient's face.

